

# Model KMF 240 | Constant climate chambers with expanded temperature / humidity range

The BINDER KMF ensures absolutely constant test conditions throughout the testing area. A big advantage of this constant climate chamber is its low space requirement and flexibility in terms of water supply. The wide temperature and humidity range make this constant climate chamber ideally suited for stress testing series.

#### **BENEFITS**

- Safe thanks to climatic homogeneity that far exceeds the accuracy required by ICH guidelines as well as THB (85/85), even with a fully loaded unit.
- Reliable thanks to failsafe operation without compromise. The interior and Longlife evaporator plate are made entirely from stainless steel.
- Smart, as a wide range of accessories makes it highly compatible for adaptation to specific customer requirements.
- Economical thanks to maximum effective volume which allows for 30% larger load compared to the competition.



Model 240

# MAIN FEATURES

- Temperature range: -10 °C to +100 °C
- Humidity range: 10 % RH to 98 % RH
- APT.line™ preheating chamber technology
- Humidity regulation with capacitive humidity sensor and vapor humidification
- Inner chamber made of stainless steel
- BINDER Multi Management Software APT-COM™ Basic Edition
- Intuitive touchscreen controller with time-segment and real-time programming
- Internal data logger, measured values can be read out in open format via USB
- · Unit self-test for comprehensive status analysis



Model 240

- Tight-sealing inner door made of safety glass (ESG)
- Avoidance of glass corrosion by special TIMELESS coating
- 1 stainless steel rack
- Access port with silicone plug, 30 mm, left
- Class 3.1 independent temperature safety device (DIN 12880) with visual and audible temperature alarm
- Computer interface: Ethernet
- Door heating

### **ORDERING INFORMATION**

Interior volume [L]	Voltage	Option model	Version	ArtNo.
247	200230 V 1~ ph 50/60 Hz	Standard	KMF240-230V	9020-0343
	200240 V 1~ ph 50/60 Hz	Standard	KMF240-240V	9020-0344




#### **TECHNICAL DATA**

umber  Ince Data Temperature  Ince Trange  The Trange Tran	9020-0343  -10100  0.8  0.4  200	9020-0344 -10100 0.8 0.4 200
eating-up rate according to IEC 60068-3-5 [K/min] colling down time according to IEC 60068-3-5 [K/min] compensation at 25 °C [W]	0.8 0.4 200	o.8 o.4
eating-up rate according to IEC 60068-3-5 [K/min] poling down time according to IEC 60068-3-5 [K/min] compensation at 25 °C [W] ace Data Climate	0.8 0.4 200	o.8 o.4
conpensation at 25 °C [W]	0.4 200	0.4
compensation at 25 °C [W]	1090	
nce Data Climate	1090	200
	<u> </u>	
ire range [°C]	<u> </u>	
0.1.1		1090
re variation depending on setpoint [± K]	0.11	0.11
re fluctuation depending on setpoint [± K]	0.10.3	0.10.3
range	1098	1098
fluctuation depending on setpoint	≤2 ± % RH	≤2 ± % RH
temperature range [°C]	590	590
data		
age [V]	200230	200240
quency [Hz]	50/60	50/60
ower [kW]	2.1	2.1
[A]	16	16
minal voltage)	1~	1~
lume [L]	247	247
t of the unit (empty) [kg]	189	189
load [kg]	100	100
ack [kg]	30	30
ance back [mm]	100	100
ance sidewise [mm]	100	100
imensions		
n]	650	650
m]	785	785
n]	485	485
rs	1	1
5	1	1
imensions not incl. fittings and connections		
[mm]	930	930
t [mm]	1465	1465
[mm]	800	800
ent-specific data		
nsumption at 85 °C and 85 % RH [Wh/h]	570	570
essure level [dB(A)]	52	52
f shelves (std./max.)	1/9	1/9


<sup>1</sup> All technical data is specified for unloaded units with standard equipment at an ambient temperature of +22 °C ±3 °C and a power supply voltage fluctuation of ±10 %. The temperature data is determined to BINDER factory standard following DIN 12880, observing the recommended wall clearances of 10 % of the height, width, and depth of the inner chamber. Technical data refers to 100 % fan speed. All indications are average values, typical for units produced in series. We reserve the right to change technical specifications at any time.



## **DIMENSIONS** incl. fittings and connections [mm]



### **CHARTS**



- ICH Long term stability testing Accelerated stability testing ICH Stress testing Industrial THB testing (85/85)
- A: Guaranteed condensation-free range
   B:Time-limited operation (max. 24 hours)
   C: Condensation in the inner chamber may be possible

Climate chart

### **OPTIONS**

Designation	Description	*	ArtNo.
	left		
	30 mm	01	8012-1446
	50 mm	01	8012-1476
	100 mm	01	8012-1342
	right		
ccess port with silicone	30 mm	01	8012-1440
lug	50 mm	01	8012-1470
	100 mm	01	8012-1339
	top		
	30 mm	01	8012-1452
	50 mm	01	8012-1458
	100 mm	01	8012-1464
llarm output, zero- oltage	for temperature ( $\pm 2$ °C) and humidity ( $\pm 5$ % RH), accessible via 6-pin DIN socket (max. 24 V - 2.5 A), with audible signal that can be switched off	-	8012-1677
analog output 4-20 mA	for temperature and humidity values (output not adjustable)	-	8012-1680
alibration certificate, xpanded	for temperature and humidity; for extending the measurement in center of chamber to include another test value	-	8012-1191

<sup>\*</sup> Notes > See last page



Designation	Description	*	ArtNo.
Calibration certificate, temperature	temperature measurement incl. certificate and 27 measuring points at specified temperature	-	8012-1606
	temperature measurement incl. certificate, 15- 18 measuring points at specified temperature	-	8012-1586
	temperature measurement incl. certificate, 9 measuring points at specified temperature	-	8012-1565
Calibration certificate, temperature and humidity	Measurement in center of chamber at 25 °C / 60% RH or at specified test values	-	8012-1185
	temperature (according to DIN1288o) and humidity measurement incl. certificate, 27 temperature measuring points and 1 humidity measuring point, at 25 $^{\circ}$ C / 60 $^{\circ}$ RH or at specified values	-	8012-1612
Class 3.3 independent emperature safety device	with visual alarm (DIN 12880)	-	8012-1674
Door lock	lockable door handle	-	8012-166
Inner chamber, reinforced	including 2 reinforced racks	-	8012-062
Pt 100 temperature sensor	additional flexible Pt 100, interior, for displaying the temperature on the unit display	-	8012-168
RS 485 interface, 2-wire	Additional serial interface can be used parallel to Ethernet, for Multi Management Software APT-COM™	_	8012-1712

<sup>\*</sup> Notes > See last page

### **ACCESSORIES**

Designation	Description	*	ArtNo.
APT-COM™ 4 GLP- Edition	for working under GLP-compliant conditions. Measured values are documented in a tamper-proof way in line with the requirements of FDA Regulation 21 CFR 11.		
cultion	version 4, GLP edition	-	9053-004
PT-COM™ 4	convenient unit and user management built on the BASIC edition. Suitable for networking up to 100 units.		
PROFESSIONAL-Edition	version 4, PROFESSIONAL edition	-	9053-004
BINDER PURE AQUA SERVICE	System for preparation or complete desalination of tap water, complete set containing PURE AQUA 300 single-use cartridge, measuring device, and all necessary connecting parts	-	8012-0759
BINDER PURE AQUA SERVICE, accessories	Single-lise replacement cartridge for RINDER PHRE ACHIA System		6011-0165
	Basic set consisting of 2 pieces, attachment material, control unit for max. 4 light strips, 100-240 V, 50/60 Hz		
	Basic set 300, length 30 cm	-	8012-1107
FD limbt have	Basic set 500, length 50 cm	-	8012-1108
.ED light bars	Expansion set consisting of 2 pieces, attachment material: clips. For expanding the basic set of light bars		
	Expansion set 300, length 30 cm	-	8012-1716
	Expansion set 500, length 50 cm	-	8012-1717
oH-neutral detergent	concentrated, for gentle remove of residual contaminants; 1 kg	-	1002-001
	IQ/OQ documents – supporting documents for validation performed by customers, consisting of: IQ/OQ checklists incl. calibration guide and comprehensive unit documentation; parameters: temperature and humidity values		
	Digital in PDF format	-	7057-000
D11614144-	Hard copy inside folder	-	7007-000
Qualification documents	IQ/OQ/PQ documents – supporting documents for validation performed by customers, according to customer requirements, PQ section added to qualification folder IQ/OQ; parameters: temperature and humidity values		
	Digital in PDF format	-	7057-000
	Hard copy inside folder	-	7007-000
Rack	stainless steel	-	8012-205
Rack accessories	fasteners (1 set of 4) for additional security of racks	-	8012-062
Rack, reinforced	stainless steel, with fasteners (1 set of 4)	-	8012-063
	RS 422 cable set and RS 485 / RS 422 interface converter for connection to 10-way plug distributor		
RS 485 / RS 422 Interface converter	115 V option model	-	8012-059
interiace converter	230 V option model	-	8012-058
Shelf, perforated	Stainless steel	_	6004-004
	consisting of fresh- and waste-water containers (20 liters each), cabling and pump		
Water supply set	external, for hanging from the back of the device	_	8012-064
	external, free-standing	_	8012-184
Notes > See last page			

<sup>\*</sup> Notes > See last page



Designation	Description	*	ArtNo.
WLAN kit	The kit contains a client bridge that establishes a wireless connection between BINDER units and APT-COM4, LIMS, or customer-specific software via an Ethernet interface. It provides an alternative solution in situations where units need to be positioned in locations without an on-site Ethernet connection. In secured networks, installation and configuration must be performed by the customer's IT service.	-	8500-0164

<sup>\*</sup> Notes > See last page

### **SERVICES**

Designation	Description	*	ArtNo.
Installation services			
Unit commissioning	Connect the unit to the customer-side connections (electricity, water, wastewater, gas), basic functions check, brief operating instructions. (excl.: unpacking, setup, controller instructions, programming, installation work)	05	DL10-0300
Unit instructions	Instruction regarding operating principle and basic functions of the unit, operation of the control electronics including programming	05	DL10-0700
Maintenance contracts			
Maintenance services			
BRONZE 3-year maintenance contract	Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts	05	DL20-0710
GOLD 3-year maintenance contract	Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts, testing of all key functions, replacement of wear parts, calibration of one temperature/humidity value, including certificate	05	DL20-0920
Maintenance	One-off maintenance service in accordance with maintenance schedule. Visual inspection of mechanical and electrical components, testing of all key functions. Calibration of a test temperature specified by the user in center of usable space without certificate	05	DL20-040
SILVER 3-year maintenance contract	Maintenance service as contractually agreed, visual inspection of mechanical and electrical components, check of control response, 20% discount on spare parts, testing of all key functions, calibration of one test temperature specified by the user in the center of the usable space, without certificate	05	DL20-082
Calibration services			
	Expansion –Temperature and humidity calibration with 1 measuring point in center of chamber with 1 specified pair of values, including certificate	03, 04, 05	DL30-030:
Temperature and humidity calibration	Temperature and humidity calibration with 1 measuring point in center of chamber with 1 specified pair of values, including certificate	03, 04, 05	DL30-030:
Temperature and humidity measurement according to DIN12880	Temperature measurement in accordance with DIN 12880 with 27 temperature measuring points and 1 humidity measuring point in center of chamber with a pair of values specified by the user, including certificate	03, 04, 05	DL30-042;
Temperature and humidity measurement, 18-1 measuring points	Temperature measurement with 18 temperature measuring points and 1 humidity measuring point in center of chamber with a pair of values specified by the user, including certificate	03, 04, 05	DL30-0318
Temperature and humidity measurement, 27-1 measuring points	Temperature measurement with 27 temperature measuring points and 1 humidity measuring point in center of chamber with a pair of values specified by the user, including certificate	03, 04, 05	DL30-032;
Temperature and humidity measurement, 9-1 measuring points	Temperature measurement with 9 temperature measuring points and 1 humidity measuring point in center of chamber with a pair of values specified by the user, including certificate	03, 04, 05	DL30-030
Validation services			
Execution of IQ/OQ	Execution of IQ/OQ in accordance with qualification folder	05	DL42-030
Execution of IQ/OQ/PQ	Execution of IQ/OQ/PQ in accordance with qualification folder	05	DL44-050
Warranty service			
	The warranty is extended by 1 year from the delivery date, wear parts are excluded		DL50-003

<sup>\*</sup> Notes > See last page



#### **NOTES**

- Condensation may occur in the area around the access port. Access ports may be placed in custom locations for an additional charge. UL mark is not granted when this option is used.
- 02
- Sensor calibration is performed in an accredited calibration laboratory. 03
- Calibration is performed according to the BINDER factory standard. 04
- Quoted prices do not include travel costs. Please refer to the chapter on BINDER Service for travel costs for your region. Quoted prices for services performed in Switzerland do not include a country-specific added fee (available on request).

### **BINDER GmbH**

Tuttlingen, Germany TEL +49 7462 2005 0 FAX +49 7462 2005 100 info@binder-world.com www.binder-world.com

BINDER Asia Pacific (Hong Kong) Ltd.

Kowloon, Hong Kong, P.R. China TEL +852 39070500 FAX +852 39070507 asia@binder-world.com www.binder-world.com

**BINDER Environmental Testing** Equipment (Shanghai) Co., Ltd. Shanghai, P.R. China TEL +86 21 685 808 25 FAX +86 21 685 808 29 china@binder-world.com www.binder-world.com

**Representative Office for CIS** 

Moscow, Russia TEL +7 495 988 15 16 FAX +7 495 988 15 17 russia@binder-world.com www.binder-world.com

**BINDER Inc.** 

Bohemia, NY, USA TEL +1 631 224 4340 FAX +1 631 224 4354 usa@binder-world.com www.binder-world.us